



SAP SPOUTS



Straight Sap Spout



PATENTED



PATENTED

To prevent from cutting the drop line, the SP225 is used with the spout adaptor FTA90-K

Polycarbonate is not recommended with alcohol.

For 3/16" tubing

Polycarbonate - Translucent		
Clear	SP316-C	\$0.16
Blue	SP316-B	\$0.17

For 5/16" tubing

Polycarbonate - Translucent		
Clear	SP225-C	\$0.14
Blue	SP225-B	\$0.15

XB2 is resistant to alcohol.


For 3/16" tubing

XB2 - Opaque			
★	Blue	SP316-XBO	\$0.23
★	Black	SP316-XKO	\$0.23
XB2 - Translucent			
★	Clear	SP316-XC	\$0.19
★	Blue	SP316-XB	\$0.19
★	Gray	SP316-XG	\$0.19

For 5/16" tubing

XB2 - Opaque			
★	Blue	SP225-XBO	\$0.21
★	Black	SP225-XKO	\$0.21
XB2 - Translucent			
★	Clear	SP225-XC	\$0.17
★	Blue	SP225-XB	\$0.17
★	Gray	SP225-XG	\$0.17

Sap Spouts .225" 115°



PATENTED



PATENTED

Polycarbonate is not recommended with alcohol.

For 3/16" tubing

Polycarbonate - Translucent		
Clear	SP316-115-225-C	\$0.16
Blue	SP316-115-225-B	\$0.17

For 5/16" tubing

Polycarbonate - Translucent		
Clear	SP115-225-C	\$0.16
Blue	SP115-225-B	\$0.17

XB2 is resistant to alcohol.

For 3/16" tubing

XB2 - Opaque			
★	Blue	SP316-115-225-XBO	\$0.23
★	Black	SP316-115-225-XKO	\$0.23
XB2 - Translucent			
★	Clear	SP316-115-225-XC	\$0.20
★	Blue	SP316-115-225-XB	\$0.20
★	Gray	SP316-115-225-XG	\$0.20

For 5/16" tubing

XB2 - Opaque			
★	Blue	SP115-225-XBO	\$0.23
★	Black	SP115-225-XKO	\$0.23
XB2 - Translucent			
★	Clear	SP115-225-XC	\$0.20
★	Blue	SP115-225-XB	\$0.20
★	Gray	SP115-225-XG	\$0.20